




BONDING BRIDGE

Intersystem Bonding Bridge Five Connections
N/A

B83.2



Catalog #: RACIBB

APPLICATIONS

For installing a grounding conductor with a lay-in style lug and multiple mounting holes for five total connections in a single location
For residential and commercial locations

PRODUCT FEATURES

For solid or stranded conductors
Zinc body, Polycarbonate cover
N/A

UL LISTED

Standard 514B, File E195975

GENERAL PRODUCT INFORMATION

Grounding Conductor Size: #6 - #2 AWG & #14 - #4 AWG

DRAWING DIMENSIONS

Dimension A: 1.378 in.
Dimension B: 4.606 in.
Dimension C: 1.575 in.

PACKAGING

Package Type: Carton
Ship Carton Qty.: 6
Product UPC-A Labeled: No
Weight (Lbs. Per/C): 43.30
Ship Carton Length (in.): 5.50
Ship Carton Width (in.): 3.07
Ship Carton Height (in.): 5.50
Ctn Weight (Lbs.): 2.60
UPC Number: 050169989579
I2of5: 50050169989574