




## COMBO (RIGID/IMC OR EMT) BODIES AND ASSEMBLIES

### Threaded Conduit Fittings: C Body Only 3/4" Rigid C Type Body

C13.1



Catalog #: RC075

#### APPLICATIONS

For use with threaded Rigid/IMC conduit, for pulling access or to split a run into multiple directions.  
N/A

#### PRODUCT FEATURES

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

#### CULUS

Listed

#### NEMA

NEMA 3R Rated

#### NEC

2014 NEC Compliant

#### GENERAL PRODUCT INFORMATION

Trade Size: 3/4"  
 Description Table: 3/4" Rigid C Type Body

#### PACKAGING

Package Type: Carton  
 Std. Pkg.: 10  
 Ship Carton Qty.: 50  
 Product UPC-A Labeled: Yes  
 Weight (Lbs. Per/C): 27  
 Ship Carton Length (in.): 20.28  
 Ship Carton Width (in.): 11.22  
 Ship Carton Height (in.): 6.50  
 Ctn Weight (Lbs.): 15.87  
 Pallet Qty: 2000  
 UPC Number: 050169816615  
 I2of5: 50050169816610