




COMBO (RIGID/IMC OR EMT) BODIES AND ASSEMBLIES

Threaded Conduit Fittings: C Body Only 2-1/2" Rigid C Type Body

C13.1



Catalog #: RC250

APPLICATIONS

For use with threaded Rigid/IMC conduit, for pulling access or to split a run into multiple directions.
N/A

PRODUCT FEATURES

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

CULUS

Listed

NEMA

NEMA 3R Rated

NEC

2014 NEC Compliant

GENERAL PRODUCT INFORMATION

Trade Size: 2-1/2"
Description Table: 2-1/2" Rigid C Type Body

PACKAGING

Package Type:	Carton
Std. Pkg.:	-
Ship Carton Qty.:	5
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	275
Ship Carton Length (in.):	13.98
Ship Carton Width (in.):	5.59
Ship Carton Height (in.):	5.12
Ctn Weight (Lbs.):	3.31
Pallet Qty:	168
UPC Number:	050169816660
I2of5:	50050169816665