



## RHC080806

by Wiegmann  
Catalog ID: RHC080806

N3R Continuous Hinge Wall-Mount 8X8X6 Carbon Steel - Gray

Designed for use as wiring boxes and junction boxes. Provide protection in outdoor installations against rain, sleet, and snow, or indoors against dripping water.

- Bodies and doors fabricated from 16 gauge carbon steel. Continuous hinge. Lid is supplied with a padlockable draw latch. Hinge is made of carbon steel with a stainless steel hinge pin. Standard size enclosures are provided with knockouts in bottom. Weldnuts provided for mounting optional back panels. External mounting plates, top and bottom of enclosure. Knockouts on bottom of enclosure. Grounding provisions provided.

## Product Details

### General

Application	Designed for use as wiring boxes and junction boxes. Provides protection in outdoor installations against rain, sleet, and snow, or indoors against dripping water.
Color	Gray
Construction	Spot Welded
Cover Type	Hinged Cover
Finish Type	Textured
Knockouts	Yes
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	External Mounting Plates
Mounting Type	Wall Mount
Type	Enclosure
UPC	786725406203

### Dimensions

Actual Depth	6.13 in
Actual Height	8.060 in
Cubic Capacity	384 cu.in
Depth	6 in

Height	8 in
Weight	8 lb
Width	8 in

**Conductor Related**

Cable Entry	Knock Outs
-------------	------------

**Certifications and Compliance**

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	NEMA 3R
UL Listed	Yes