



RHC242008

by Wiegmann
Catalog ID: RHC242008

N3R Continuous Hinge Wall-Mount 24X20X8 Carbon Steel - Gray

Designed for use as wiring boxes and junction boxes. Provide protection in outdoor installations against rain, sleet, and snow, or indoors against dripping water.

- Bodies and doors fabricated from 14 gauge carbon steel. Continuous hinge. Hinge is made of galvanized steel with a stainless steel pin. No knockouts. Collar studs provided for mounting optional back panels. External mounting plates, top and bottom of enclosure. Hasp and staple provided for padlocking. Grounding provisions provided.

Product Details

General

Application	Designed for use as wiring boxes and junction boxes. Provides protection in outdoor installations against rain, sleet, and snow, or indoors against dripping water.
Color	Gray
Construction	Seam and Tack Welded
Cover Type	Hinged Cover
Finish Type	Smooth
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	External Mounting Plates
Mounting Type	Wall Mount
Type	Enclosure
UPC	786725406753

Dimensions

Cubic Capacity	3840 cu.in
Depth	8 in
Height	24 in
Weight	56 lb

Width	20 in
-------	-------

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	NEMA 3R
UL Listed	Yes