




**RIGID BODIES AND ASSEMBLIES**

LR Assembly  
N/A

C13



Catalog #: RLR250

**APPLICATIONS**

For use with threaded rigid/IMC conduit for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.  
N/A

**PRODUCT FEATURES**

- Durable die cast aluminum construction
- Premium powder coat finish
- Includes NBR synthetic rubber gasket
- Stamped aluminum cover
- Combination head screw

**UL LISTED**

File E331564

**NEMA**

NEMA 3R rated

**NEC**

2014 NEC® compliant

**GENERAL PRODUCT INFORMATION**

Trade Size: 2-1/2 in.

**DRAWING DIMENSIONS**

- Dimension A: 12.83 in.
- Dimension B: 5.89 in.
- Dimension C: 3.98 in.
- Dimension D: 4.49 in.
- Dimension E: 11.250 in.
- Dimension F: Tapped holes #5/16UNC-2B
- Dimension G: 2-1/2-8NPT
- Dimension H: 2.459 in.

**PRODUCT MEASUREMENTS**

Cubic Inches (cm3): 157.3 (2578)

**PACKAGING**

- Package Type: Carton
- Ship Carton Qty.: 1
- Product UPC-A Labeled: Yes
- Weight (Lbs. Per/C): 442.00
- Ship Carton Length (in.): 11.02
- Ship Carton Width (in.): 5.59
- Ship Carton Height (in.): 7.48
- Ctn Weight (Lbs.): 4.42
- UPC Number: 092326213387
- I2of5: 30092326213388