




RIGID BODIES AND ASSEMBLIES

LR Assembly
N/A

C13



Catalog #: RLR350

APPLICATIONS

For use with threaded rigid/IMC conduit for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.
N/A

PRODUCT FEATURES

- Durable die cast aluminum construction
- Premium powder coat finish
- Includes NBR synthetic rubber gasket
- Stamped aluminum cover
- Combination head screw

UL LISTED

File E331564

NEMA

NEMA 3R rated

NEC

2014 NEC® compliant

GENERAL PRODUCT INFORMATION

Trade Size: 3-1/2 in.

DRAWING DIMENSIONS

- Dimension A: 15.65 in.
- Dimension B: 7.66 in.
- Dimension C: 5.59 in.
- Dimension D: 5.55 in.
- Dimension E: 13.687 in.
- Dimension F: Tapped holes #5/16UNC-2B
- Dimension G: 3-1/2-8NPT
- Dimension H: 3.538 in.

PRODUCT MEASUREMENTS

Cubic Inches (cm3): 323.0 (5293.0)

PACKAGING

- Package Type: Carton
- Ship Carton Qty.: 1
- Product UPC-A Labeled: Yes
- Weight (Lbs. Per/C): 688.00
- Ship Carton Length (in.): 13.98
- Ship Carton Width (in.): 7.48
- Ship Carton Height (in.): 6.69
- Ctn Weight (Lbs.): 6.88
- UPC Number: 092326213400
- I2of5: 30092326213401