




RIGID BODIES AND ASSEMBLIES

LR Assembly
N/A

C13



Part Number	Material	Finish	Weight	Volume	Dimensions	Notes
RLR400	Aluminum	Powder Coat	1.2	323.0	15.65 x 7.66 x 5.59	



Catalog #: RLR400

APPLICATIONS

For use with threaded rigid/IMC conduit for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.
N/A

PRODUCT FEATURES

- Durable die cast aluminum construction
- Premium powder coat finish
- Includes NBR synthetic rubber gasket
- Stamped aluminum cover
- Combination head screw

UL LISTED

File E331564

NEMA

NEMA 3R rated

NEC

2014 NEC® compliant

GENERAL PRODUCT INFORMATION

Trade Size: 4 in.

DRAWING DIMENSIONS

- Dimension A: 15.65 in.
- Dimension B: 7.66 in.
- Dimension C: 5.59 in.
- Dimension D: 5.55 in.
- Dimension E: 13.687 in.
- Dimension F: Tapped holes #5/16UNC-2B
- Dimension G: 4-8NPT
- Dimension H: 4.016 in.

PRODUCT MEASUREMENTS

Cubic Inches (cm³): 323.0 (5293.0)

PACKAGING

- Package Type: Carton
- Ship Carton Qty.: 1
- Product UPC-A Labeled: Yes
- Weight (Lbs. Per/C): 642.00
- Ship Carton Length (in.): 16.93
- Ship Carton Width (in.): 7.48
- Ship Carton Height (in.): 6.69
- Ctn Weight (Lbs.): 6.42
- UPC Number: 092326213417
- I2of5: 30092326213418