



* Representative image

RSC121208NK

by Wiegmann

Catalog ID: RSC121208NK

Prop65_Cancer&Reproductive

N3R Screw-Cover Wall-Mount No Knockouts 12X12X8 Carbon Steel - Gra

- Bodies and doors fabricated from 16 gauge carbon steel. Drip shield top and smooth seamless sides and front. A slip-on reversible cover is securely fastened with screws located along bottom edge. No gasketing is required. Hasp for padlocking or meter seal is provided.

Product Details

General

Application	Designed for use as wiring boxes and junction boxes. Provide protection in outdoor applications against rain, sleet, and snow, or indoors against dripping water.
Color	Ansi-61 Gray Textured
Construction	Spot Welded
Cover Type	Screw Cover
Finish Type	Textured
Knockouts	No
Listings	UL, CSA
Material	Steel, Carbon
Mounting Method	Embossed Mounting Holes
Mounting Type	Embossed Mounting Holes
Type	Enclosure
UPC	786725875504

Dimensions

Cubic Capacity	1152 cu.in
Depth	8 in
Height	12 in
Weight	13 lb
Width	12 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"> UL CSA
Nema Rating	3R
UL Listed	Yes

