



RSC242408G

by Wiegmann
Catalog ID: RSC242408G

N3R Screw-Cover Wall-Mount 24X24X8 Carbon Steel - Galvanized

RSC SERIES - 14 GAUGE PRE-GALVANIZED STEEL NEMA 3R SCREW COVER WALL-MOUNT - ENCLOSURE SIZE 24 IN X 24 IN X 8 IN.

- Bodies and doors fabricated from 14 gauge pre-galvanized steel. Drip shield top and smooth seamless sides and front. A slip-on reversible cover is securely fastened with screws located along bottom edge. No gasketing is required. Hasp for padlocking or meter seal is provided.

Product Details

General

Application	Designed for use as wiring boxes and junction boxes. Provide protection in outdoor applications against rain, sleet, and snow, or indoors against dripping water.
Construction	Tack Welded
Cover Type	Screw Cover
Finish Type	Galvanized
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Mounting Holes
Mounting Type	Mounting Holes
Type	Enclosure
UPC	786725403165

Dimensions

Cubic Capacity	4608 cu.in
Depth	8 in
Height	24 in
Weight	46 lb
Width	24 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	NEMA 3R
UL Listed	Yes