



RSCG101018GNK

by Wiegmann
Catalog ID: RSCG101018GNK

N3R Gutter - No Knockouts 10X10X18 Carbon Steel - Galvanized

- Trough and cover fabricated from 16 gauge G-90 pre-galvanized steel. Drip shield top and smooth seamless sides, front and back, prevent rain, snow, and sleet from entering the enclosure. Embossed mounting holes are conveniently located on the back. A slip-on removable cover is securely fastened with screws located along the bottom edge.

Product Details

General

| | |
|-----------------|--|
| Application | Designed to protect wiring in outdoor installations against rain, sleet and snow, or indoors against dripping water. |
| Construction | Spot and Tack Welded |
| Finish Type | Galvanized |
| Knockouts | No |
| Listings | UL, CSA |
| Material | Carbon Steel |
| Mounting Method | Embossed mounting holes |
| Type | Gutter |
| UPC | 786725875245 |

Dimensions

| | |
|----------------|------------|
| Actual Depth | 18.13 in |
| Actual Height | 10.060 in |
| Actual Width | 10.060 in |
| Cubic Capacity | 1800 cu.in |
| Depth | 18 in |
| Height | 10 in |
| Weight | 20 lb |
| Width | 10 in |

Certifications and Compliance

| | |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none">• UL• CSA |
| Nema Rating | 3R |
| UL Listed | Yes |