



## RSCG101036NK

by Wiegmann  
Catalog ID: RSCG101036NK

N3R Gutter - No Knockouts 10X10X36 Carbon Steel - Gray

- Trough and cover fabricated from 16 gauge carbon steel. Drip shield top and smooth seamless sides, front and back, prevent rain, snow, and sleet from entering the enclosure. Embossed mounting holes are conveniently located on the back. A slip-on removable cover is securely fastened with screws located along the bottom edge.

### Product Details

#### General

|                 |  |
|-----------------|--|
| Application     | Designed to protect wiring in outdoor installations against rain, sleet and snow, or indoors against dripping water. |
| Color           | Gray   |
| Construction    | Spot and Tack Welded   |
| Finish Type     | Polyester Powder   |
| Knockouts       | No   |
| Listings        | UL, CSA  |
| Material        | Carbon Steel   |
| Mounting Method | Embossed mounting holes  |
| Type            | Gutter   |
| UPC             | 786725875207   |

#### Dimensions

|                |            |
|----------------|------------|
| Actual Depth   | 36.13 in   |
| Actual Height  | 10.060 in  |
| Actual Width   | 10.060 in  |
| Cubic Capacity | 3600 cu.in |
| Depth          | 36 in      |
| Height         | 10 in      |
| Weight         | 23 lb      |
| Width          | 10 in      |

## Certifications and Compliance

|                  |  |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul> |
| Nema Rating      | 3R   |
| UL Listed        | Yes  |