




**RIGID BODIES AND ASSEMBLIES**

Service Entrance Elbow  
N/A

C13



CATALOG NUMBER	CONDUIT SIZE	A	B	C
RSLB50	1/2"	1.587	1.266	3.25
RSLB75	3/4"	1.878	1.593	3.663
RSLB100	1"	2.087	1.917	4.272
RSLB125	1-1/4"	2.579	2.39	5.506
RSLB150	1-1/2"	2.997	2.654	6.217
RSLB200	2"	3.075	3.122	6.715



Catalog #: RSLB125

**APPLICATIONS**

For use with threaded rigid/IMC conduit for pulling access or to split a run into multiple directions. Removable cover allows access for maintenance and making taps and splices to conductors.

N/A

**PRODUCT FEATURES**

- Durable die cast aluminum construction
- Premium powder coat finish
- Includes NBR synthetic rubber gasket
- Stamped aluminum cover
- Combination head screw

**UL LISTED**

File E331564

**NEMA**

NEMA 3R rated

**NEC**

2014 NEC® compliant

**GENERAL PRODUCT INFORMATION**

Trade Size: 1-1/4 in.

**DRAWING DIMENSIONS**

Dimension A: 2.579 in.  
 Dimension B: 2.39 in.  
 Dimension C: 5.506 in.

**PACKAGING**

Package Type: Carton  
 Ship Carton Qty.: 2  
 Product UPC-A Labeled: Yes  
 Weight (Lbs. Per/C): 70.00  
 Ship Carton Length (in.): 6.75  
 Ship Carton Width (in.): 3.63  
 Ship Carton Height (in.): 7.13  
 Ctn Weight (Lbs.): 1.40  
 UPC Number: 092326212489  
 I2of5: 30092326212480