



S2224G

by Wiegmann
Catalog ID: S2224G

N1 Screw-Cover Wireway 2.5X2.5X24 Carbon Steel - Galvanized

- Bodies and covers are fabricated from 16 gauge pre-galvanized steel. S Series screw cover design covers held firmly in place with captivated screw fasteners. Straight sections with knockouts are provided on side walls on wireways.

Product Details

General

Application	Designed to protect electrical wiring in applications where dirt, dust, oil, and water are not serious problems. All sections are open on one side so wires and cable can be laid in along an entire wireway run.
Cover Type	Screw Cover
Enclosure Type	Nema 1 Type Enclosure
Finish Type	Galvanized
Knockouts	Yes
Listings	UL, CSA
Material	Carbon Steel
Type	Wireway
UPC	786725851478

Dimensions

Actual Height	2.500 in
Actual Length	24.000 in
Actual Width	2.500 in

Depth	24 in
Height	3 in
Weight	18 lb
Width	3 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	1
UL Listed	Yes