



S2272GNK

by Wiegmann
Catalog ID: S2272GNK

N1 Screw-Cover Wireway - No Knockouts 2.5X2.5X72 Carbon Steel - Galvanized

- Bodies and covers are fabricated from 16 gauge pre-galvanized steel. S Series screw cover design covers held firmly in place with captivated screw fasteners.

Product Details

General

Application	Designed to protect electrical wiring in applications where dirt, dust, oil, and water are not serious problems. All sections are open on one side so wires and cable can be laid in along an entire wireway run.
Cover Type	Screw Cover
Enclosure Type	Nema 1 Type Enclosure
Finish Type	Galvanized
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Type	Wireway
UPC	786725851560

Dimensions

Actual Height	2.500 in
Actual Length	72.000 in
Actual Width	2.500 in
Depth	72 in
Height	3 in
Weight	54 lb
Width	3 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	1
UL Listed	Yes