

# SSBC350-4SIV

by CMC

Catalog ID: SSBC350-4SIV



Rubber Insulated Secondary Connectors, Standard spacing, Dual rated connectors for Aluminum or Copper conductors, Orange screw plugs available

- Clear plated for low-contact resistance.
- Meets the performance requirements of ANSI C119.1, ANSI C119.4 and Western Underground Committee Guide 2.5.
- Supplied with aluminum set-screws.
- Includes silicone grease and CO-OX oxide inhibitor.
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- Each unit individually wrapped and labeled for ease of identification and cleanliness.
- For installation, CMC® recommends the use of a 9" insulated hex wrench (no tee handles).
- A torque wrench should be used to ensure the proper torque achieved.

## Product Details

### General

Material	Aluminum Alloy, 6061-T6
UPC	621945429789

### Dimensions

Height	2.46 in
Length	4.72 in
Width	4.06 in

### Electrical Ratings

Voltage Rating	600 V
----------------	-------

### Conductor Related

Number Of Conductors	4
----------------------	---



**CONNECTOR MANUFACTURING COMPANY**  
3501 Symmes Road  
Hamilton, Ohio 45015 - 1369  
513 - 860 - 4455(Press 2 for Customer Service and Sales)  
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

