



SSN4X603712

by Wiegmann
Catalog ID: SSN4X603712

N4X Single Door Flanged Disconnect 60X37X12 304 Stainless Steel

Product Details

General

Application	These general purpose disconnect enclosures accept major brand disconnect switches and circuit breakers.
Construction	Continuously Welded Seams
Finish Type	Smooth Grained
Latches Type	Clamps
Listings	UL, CSA
Material	304 Stainless Steel
Mounting Method	External mounting feet
Number of Doors (Fixed)	1
Type	Enclosure
UPC	786725369904

Dimensions

Actual Depth	12.13 in
Actual Width	37.380 in
Cubic Capacity	26640 cu.in
Depth	12 in
Height	60 in
Weight	188 lb
Width	37 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	4X
UL Listed	Yes