




COMBO (RIGID/IMC OR EMT) BODIES AND ASSEMBLIES

Threaded Conduit Fittings: T Body Only 3/4" Rigid T Type Body

C13.1



Catalog #: T075

APPLICATIONS

For use with threaded Rigid/IMC conduit, for pulling access or to split a run into multiple directions.
N/A

PRODUCT FEATURES

Durable die cast aluminum construction
Premium powder coat finish
Combination head screw

CULUS

Listed

NEMA

NEMA 3R Rated

NEC

2014 NEC Compliant

GENERAL PRODUCT INFORMATION

Trade Size: 3/4"
Description Table: 3/4" Rigid T Type Body

PACKAGING

Package Type: Carton
Std. Pkg.: 10
Ship Carton Qty.: 50
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 30
Ship Carton Length (in.): 22.05
Ship Carton Width (in.): 12.01
Ship Carton Height (in.): 6.50
Ctn Weight (Lbs.): 18.30
Pallet Qty: 1500
UPC Number: 050169817018
I2of5: 50050169817013