



* Representative image

T111684

by Acme Electric
Catalog ID: T111684

Prop65_Cancer&Reproductive

Buck-Boost Transformer - Single Phase, 120 X 240 - 12/24V, 1.5kVA

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in kVA

Product Details

General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	120 X 240 V
Product Category	Buck-Boost Transformer
Secondary Voltage	12/24 V
UL Insulation Class	180°C
UPC	047503171707
Winding Material	CU
kVA	1.5

Dimensions

Height	11.62 in
Length	5.13 in
Weight	30 lb
Width	5.5 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	120 X 240 V

Certifications and Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 3R
UL Standard	UL 506