



\* Representative image

## T113073

by Acme Electric  
Catalog ID: T113073

Prop65\_Cancer&Reproductive

Buck-Boost Transformer - Single Phase, 120 X 240 - 16/32V, 1kVA

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in kVA

## Product Details

### General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	120 X 240 V
Product Category	Buck-Boost Transformer
Secondary Voltage	16/32 V
UL Insulation Class	180°C
UPC	047503084472
Winding Material	CU
kVA	1

### Dimensions

Height	10.5 in
Length	5.13 in
Weight	24 lb
Width	5.5 in

### Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	120 X 240 V

### Certifications and Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 3R
UL Standard	UL 506