



T121224CH

by Wiegmann
Catalog ID: T121224CH

N1 Hinged-Cover Wire Trough 12X12X24 Carbon Steel - Gray

Designed to protect wiring from dirt, dust, oil and water.

- Trough and cover fabricated from 14 gauge steel. Continuously welded seams ground smooth, less knockouts or holes. Oil resistant gasket and adhesive are provided. Trough comes complete with easy to operate external clamps and a continuous hinge. External mounting feet are provided.

Product Details

General

Accessory Type	Trough
Application	Designed to protect from dirt, dust, oil, and water.
Color	Gray
Cover Type	Hinged Cover
Enclosure Type	Nema 12 Type Enclosure
Finish Type	Polyester Powder
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Type	Trough
UPC	786725326778

Dimensions

Actual Length	24.000 in
Depth	24 in
Height	12 in
Weight	34 lb
Width	12 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	NEMA 12
UL Listed	Yes