



* Representative image

T137922

by Acme Electric
Catalog ID: T137922

Prop65_Cancer&Reproductive

Buck-Boost Transformer - Single Phase, 240 X 480 - 24/48V, 2kVA

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in kVA

Product Details

General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240 X 480
Product Category	Buck-Boost Transformer
Secondary Voltage	24/48 V
UL Insulation Class	180°C
UPC	047503086308
Winding Material	CU
kVA	2

Dimensions

Height	7.16 in
Length	3.67 in
Weight	38 lb
Width	3.89 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 X 480 V

Certifications and Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 3R
UL Standard	UL 506