




COMBO (RIGID/IMC OR EMT) BODIES AND ASSEMBLIES

Threaded Conduit Fittings: T Body Only 1-1/2" Rigid T Type Body

C13.1



Catalog #: T150

APPLICATIONS

For use with threaded Rigid/IMC conduit, for pulling access or to split a run into multiple directions.
N/A

PRODUCT FEATURES

Durable die cast aluminum construction
Premium powder coat finish
Combination head screw

CULUS

Listed

NEMA

NEMA 3R Rated

NEC

2014 NEC Compliant

GENERAL PRODUCT INFORMATION

Trade Size: 1-1/2"
Description Table: 1-1/2" Rigid T Type Body

PACKAGING

Package Type: Carton
Std. Pkg.: 2
Ship Carton Qty.: 10
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 86
Ship Carton Length (in.): 21.65
Ship Carton Width (in.): 7.09
Ship Carton Height (in.): 9.65
Ctn Weight (Lbs.): 11.02
Pallet Qty: 480
UPC Number: 050169817049
I2of5: 50050169817044