



* Representative image

T160832

by Acme Electric

Catalog ID: T160832

Prop65_Cancer&Reproductive

Appliance Transformer - Single Phase, 200/220/240 - 115V, 400VA

Product Details

General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Product Category	Appliance Transformers
Secondary Voltage	1115 V
UL Insulation Class	180°C
UPC	047503001219
Winding Material	CU

Dimensions

Height	9.16 in
Length	3.67 in
Weight	8 lb
Width	3.89 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	200/220/240 V

Certifications and Compliance

Nema Rating	NEMA 2
-------------	--------