



\* Representative image

## T160834

by Acme Electric

Catalog ID: T160834

Prop65\_Cancer&amp;Reproductive

Appliance Transformer - Single Phase, 200/220/240 - 115V, 1000VA

### Product Details

#### General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Product Category	Appliance Transformers
Secondary Voltage	1115 V
UL Insulation Class	180°C
UPC	047503085998
Winding Material	CU

#### Dimensions

Height	9.68 in
Length	4.51 in
Weight	14 lb
Width	4.75 in

#### Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	200/220/240 V

#### Certifications and Compliance

Nema Rating	NEMA 2
-------------	--------