



* Representative image

T160835

by Acme Electric

Catalog ID: T160835

Prop65_Cancer&Reproductive

Appliance Transformer - Single Phase, 200/220/240 - 115V, 2000VA

Product Details

General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Product Category	Appliance Transformers
Secondary Voltage	1115 V
UL Insulation Class	180°C
UPC	047503001233
Winding Material	CU

Dimensions

Height	11.5 in
Length	7.13 in
Weight	27 lb
Width	7.81 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	200/220/240 V

Certifications and Compliance

Nema Rating	NEMA 2
-------------	--------