



* Representative image

T169432

by Acme Electric
Catalog ID: T169432

Prop65_Cancer&Reproductive

Power Conditioning - Hardwired Models, 95-132 X 166-228 X 192-264 X 384-528 - 120/208/240V, 0.5kVA

- Suppressing transient spikes and surges
- Rapid response to line and load changes
- Inherent overload and short circuit protection

Product Details

General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Floor/Wall
Primary Voltage	95-132 X 166-228 X 192-264 X 384-528
Product Category	Power Conditioning
Secondary Voltage	120/208/240 V
UL Insulation Class	180°C
UPC	047503087732
Winding Material	CU
kVA	0.5

Dimensions

Height	17 in
Length	7.3 in
Weight	53 lb
Width	7 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	95-132 X 166-228 X 192-264 X 384-528 V

Certifications and Compliance

CSA Standard	C22.2 No. 66
Nema Rating	NEMA 2
UL Standard	UL 1012