



* Representative image

T169434

by Acme Electric
Catalog ID: T169434

Prop65_Cancer&Reproductive

Power Conditioning - Hardwired Models, 95-132 X 166-228 X 192-264 X 384-528 - 120/208/240V, 1kVA

- Suppressing transient spikes and surges
- Rapid response to line and load changes
- Inherent overload and short circuit protection

Product Details

General

| | |
|----------------------|--------------------------------------|
| Construction | Encapsulated |
| Max Temperature Rise | 115 Degrees Celsius |
| Mounting Type | Floor/Wall |
| Primary Voltage | 95-132 X 166-228 X 192-264 X 384-528 |
| Product Category | Power Conditioning |
| Secondary Voltage | 120/208/240 V |
| UL Insulation Class | 180°C |
| UPC | 047503694343 |
| Winding Material | CU |
| kVA | 1 |

Dimensions

| | |
|--------|---------|
| Height | 18.5 in |
| Length | 8.55 in |
| Weight | 82 lb |
| Width | 6.5 in |

Electrical Ratings

| | |
|------------------|--|
| Frequency Rating | 60 Hz |
| Primary Voltage | 95-132 X 166-228 X 192-264 X 384-528 V |

Certifications and Compliance

| | |
|--------------|--------------|
| CSA Standard | C22.2 No. 66 |
| Nema Rating | NEMA 2 |
| UL Standard | UL 1012 |