



* Representative image

T179615S

by Acme Electric
Catalog ID: T179615S

Low Voltage Lighting Transformer - Single Phase, 240 - 24V, 100VA

- Copper lead wires for hardwiring
- Primary and secondary overload protection
- Full fault current carrying Farady Shield
- Single and dual knockouts

Product Details

General

Circuit Breaker Style	Push To Reset Thermal Breaker
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240
Product Category	Low Voltage Lighting Transformer
Secondary Voltage	24 V
UL Insulation Class	180°C
UPC	047503410189
Winding Material	CU

Dimensions

Height	9.01 in
Length	3.88 in
Weight	1 lb
Width	4.08 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 V

Certifications and Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 2
UL Standard	UL 506