



* Representative image

T179622S

by Acme Electric
Catalog ID: T179622S

Prop65_Cancer&Reproductive

Low Voltage Lighting Transformer - Single Phase, 120 - 12V, 600VA

- Copper lead wires for hardwiring
- Primary and secondary overload protection
- Full fault current carrying Farady Shield
- Single and dual knockouts

Product Details

General

Circuit Breaker Style	Magnetic Toggle On/Off Breaker
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	120 V
Product Category	Low Voltage Lighting Transformer
Secondary Voltage	12 V
UL Insulation Class	180°C
UPC	047503410288
Winding Material	CU

Dimensions

Height	11.68 in
Length	4.57 in
Weight	15 lb
Width	4.66 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	120 V

Certifications and Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 2
UL Standard	UL 506