



* Representative image

T181058

by Acme Electric
Catalog ID: T181058

Prop65_Cancer&Reproductive

Buck-Boost Transformer - Single Phase, 120 X 240 - 16/32V, 500VA

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in kVA

Product Details

General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	120 X 240 V
Product Category	Buck-Boost Transformer
Secondary Voltage	16/32 V
UL Insulation Class	180°C
UPC	047503176108
Winding Material	CU
kVA	0.50

Dimensions

Height	9.06 in
Length	4.2 in
Weight	15 lb
Width	4.37 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	120 X 240 V

Certifications and Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 3R
UL Standard	UL 506