



\* Representative image

## T181066

by Acme Electric  
Catalog ID: T181066

Prop65\_Cancer&Reproductive

Buck-Boost Transformer - Single Phase, 240 X 480 - 24/48V, 750VA

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in kVA

## Product Details

### General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240 X 480
Product Category	Buck-Boost Transformer
Secondary Voltage	24/48 V
UL Insulation Class	180°C
UPC	047503088128
Winding Material	CU
kVA	0.75

### Dimensions

Height	14.38 in
Length	7.13 in
Weight	19 lb
Width	10.31 in

### Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	240 X 480 V

### Certifications and Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 3R
UL Standard	UL 506