



T2224CH

by Wiegmann
Catalog ID: T2224CH

N1 Hinged-Cover Wire Trough 2.5X2.5X24 Carbon Steel - Gray

Designed to protect wiring from dirt, dust, oil and water.

- Trough and cover fabricated from 14 gauge steel. Continuously welded seams ground smooth, less knockouts or holes. Oil resistant gasket and adhesive are provided. Trough comes complete with easy to operate external clamps and a continuous hinge. External mounting feet are provided.

Product Details

General

| | |
|----------------|--|
| Accessory Type | Trough |
| Application | Designed to protect from dirt, dust, oil, and water. |
| Color | Gray |
| Cover Type | Hinged Cover |
| Enclosure Type | Nema 12 Type Enclosure |
| Finish Type | Polyester Powder |
| Knockouts | No |
| Listings | UL, CSA |
| Material | Carbon Steel |
| Type | Trough |
| UPC | 786725326266 |

Dimensions

| | |
|---------------|-----------|
| Actual Height | 2.500 in |
| Actual Length | 24.000 in |
| Actual Width | 2.500 in |
| Depth | 24 in |
| Height | 3 in |
| Weight | 6 lb |
| Width | 3 in |

Certifications and Compliance

| | |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none">• UL• CSA |
| Nema Rating | NEMA 12 |
| UL Listed | Yes |