



\* Representative image

## T3030K0013BK13S

by Acme Electric  
Catalog ID: T3030K0013BK13S

Prop65\_Cancer&Reproductive

Non Linear Load Transformer - Three Phase, 480Δ - 208Y/120V, 30kVA, K13

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection

### Product Details

#### General

ANFC Taps	2
BNFC Taps	4
Construction	Ventilated
Electrostatic Shield	Shielded
K Factor	13
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	480Δ
Product Category	Non Linear Load Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503093740
Winding Material	AL
kVA	30

#### Dimensions

Height	25.5 in
Length	19.37 in
Weight	441 lb
Width	24.39 in

#### Electrical Ratings

Efficiency	98.23%
Frequency Rating	60 Hz
Primary Voltage	480D V

## Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R
UL Standard	UL 1561