



* Representative image

T3030K0013BK20S

by Acme Electric

Catalog ID: T3030K0013BK20S

Prop65_Cancer&Reproductive

Non Linear Load Transformer - Three Phase, 480Δ - 208Y/120V, 30kVA, K20

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection

Product Details

General

| | |
|----------------------|-----------------------------|
| ANFC Taps | 2 |
| BNFC Taps | 4 |
| Construction | Ventilated |
| Electrostatic Shield | Shielded |
| K Factor | 20 |
| Max Temperature Rise | 150 Degrees Celsius |
| Mounting Type | Floor |
| Primary Voltage | 480Δ |
| Product Category | Non Linear Load Transformer |
| Secondary Voltage | 208Y/120 V |
| Taps % Steps | 2.5% |
| UL Insulation Class | 220°C |
| UPC | 047503093900 |
| Winding Material | AL |
| kVA | 30 |

Dimensions

| | |
|--------|----------|
| Height | 25.5 in |
| Length | 19.37 in |
| Weight | 441 lb |
| Width | 24.39 in |

Electrical Ratings

| | |
|------------------|--------|
| Efficiency | 98.23% |
| Frequency Rating | 60 Hz |
| Primary Voltage | 480D V |

Certifications and Compliance

| | |
|---------------------------|--|
| CSA Standard | C22.2 No. 47 |
| Dept of Energy Regulation | Meets or exceed U.S. DOE 10 CFR Part 431 |
| Nema Rating | NEMA 3R |
| UL Standard | UL 1561 |