


COMBO (RIGID/IMC OR EMT) BODIES AND ASSEMBLIES

Threaded Conduit Fittings: T Body Only
3-1/2" Rigid T Type Body

C13.1



TRADE SIZE	CATALOG NUMBER	A	B	C	D	E	F
3-1/2"	T350	96.50 (3.84)	74.6 (2.94)	124.5 (4.90)	124.5 (4.90)	124.5 (4.90)	149.5 (5.90)



Catalog #: T350

APPLICATIONS

For use with threaded Rigid/IMC conduit, for pulling access or to split a run into multiple directions.
 N/A

PRODUCT FEATURES

- Durable die cast aluminum construction
- Premium powder coat finish
- Combination head screw

CULUS

Listed

NEMA

NEMA 3R Rated

NEC

2014 NEC Compliant

GENERAL PRODUCT INFORMATION

Trade Size: 3-1/2"
 Description Table: 3-1/2" Rigid T Type Body

PACKAGING

Package Type: Carton
 Std. Pkg.: -
 Ship Carton Qty.: 1
 Product UPC-A Labeled: Yes
 Weight (Lbs. Per/C): 700
 Ship Carton Length (in.): 16.93
 Ship Carton Width (in.): 8.07
 Ship Carton Height (in.): 6.69
 Ctn Weight (Lbs.): 7.83
 Pallet Qty: 60
 UPC Number: 050169817087
 I2of5: 50050169817082