



* Representative image

T3795511S

by Acme Electric
Catalog ID: T3795511S

Prop65_Cancer&Reproductive

380Δ Primary Volts - 220Y/127 Secondary Volts - 3Ø.

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

BNFC Taps	2
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Floor
Primary Voltage	380Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	220Y/127 V
Taps % Steps	5.0%
UL Insulation Class	180°C
UPC	047503795514
Winding Material	AL
kVA	15

Dimensions

Height	20.8 in
Length	10.2 in
Weight	435 lb
Width	20.9 in

Electrical Ratings

Frequency Rating	50 Hz
Primary Voltage	380D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R

UL Standard	UL 506
-------------	--------