




## COMBO (RIGID/IMC OR EMT) BODIES AND ASSEMBLIES

### Threaded Conduit Fittings: T Body Only 4" Rigid T Type Body

C13.1



TRADE SIZE	CATALOG NUMBER	A	B	C	D	E	F
4"	T400	16.50 (418)	7.62 (194)	3.15 (80)	1.50 (38)	1.50 (38)	1.875 (47.6)



Catalog #: T400

#### APPLICATIONS

For use with threaded Rigid/IMC conduit, for pulling access or to split a run into multiple directions.  
N/A

#### PRODUCT FEATURES

Durable die cast aluminum construction  
Premium powder coat finish  
Combination head screw

#### CULUS

Listed

#### NEMA

NEMA 3R Rated

#### NEC

2014 NEC Compliant

#### GENERAL PRODUCT INFORMATION

Trade Size: 4"  
Description Table: 4" Rigid T Type Body

#### PACKAGING

Package Type:	Carton
Std. Pkg.:	-
Ship Carton Qty.:	1
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	645
Ship Carton Length (in.):	16.93
Ship Carton Width (in.):	8.07
Ship Carton Height (in.):	6.69
Ctn Weight (Lbs.):	7.28
Pallet Qty:	60
UPC Number:	050169817094
I2of5:	50050169817099