




* Representative image

Jumper Set for Hotstick Applications - 15kV, 15' 4/0 Cable

by CHANCE Utility
Catalog ID: T6010288

15kV, 15' of 4/0 cable, insulated jumper for hotstick applications, main line range of 0.162" to 1.5"

- Meets ASTM F2321 Standard Specification
- Two C-type grounding clamps (C6001743) and two threaded copper ferrules
- Main Line Range: #6 solid copper (0.162") through 1590kcmil ACSR (1.50")
- 15kV EPR-insulated jumper cable
- Other clamps and cable combinations available upon request

Product Details

General

Style	Hotstick Applied
Torque Rating	250 in-lbs
UPC	096359061915

Dimensions

Weight	23.52 lb
--------	----------

Electrical Ratings

Current Rating	400 A
Voltage Rating	15 kV

Conductor Related

Conductor Diameter (Main) - Maximum	1.5 in
Conductor Diameter (Main) - Minimum	0.162 in
Conductor Size	4/0 AWG

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com