

Masonry Box, 2-1/2 In. Deep, 28 Cu. In., 2-Gang Masonry Box, 3-13/16 In. Width, 3-3/4 Height, Raised Ground Screw, With Concentric, 1/2 & 3/4 In. Ko (10-Pack), MBS2K

By TradeSelect
Catalog # [MBS2K](#)



Masonry Box, 2-1/2 in. Deep, 28 Cu. In., 2-Gang Masonry Box, 3-13/16 in. Width, 3-3/4 Height, Raised ground screw, with Concentric, 1/2 & 3/4 in. KO (10-Pack)

Application

Masonry boxes are used for the flush installation of devices in masonry construction.

Specifications

Certified Listed CSA

Configuration

Gangable No
Number of Gang(s) 2-Gang
Knockouts 12 x 1/2-3/4 in Combination
Bracket Type No Bracket

Dimensions

Weight 0.86 lb.
Knockouts - Bottom 4 x 1/2-3/4in Combination

Knockouts - End
Actual Depth
Knockouts - Side
Raised Ground

4 x 1/2-3/4in Combination
2.53 in
4 x 1/2-3/4in Combination
Yes

General

Drawn or Welded	Welded
Color	Gray
Plaster Ears	No
UPC	626463002841
Type	Masonry Box, Box
Wiring System	Conduit
Material	Steel

Logistics

Pallet Quantity	990
Carton Quantity	10