



\* Representative image

## TF249873S

by Acme Electric  
Catalog ID: TF249873S

Prop65\_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 190/200/208/220  
380/400/416/440 - 120/240V, 3kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## Product Details

### General

CE Compliant	CE Marked
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	190 / 200 / 208 / 220 X 380 / 400 / 416 / 440 V
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503087305
Winding Material	CU
kVA	3

### Dimensions

Height	11.5 in
Length	7.13 in
Weight	55 lb
Width	10.31 in

### Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	190/200/208/220 X 380/400/416/440 V

#### Certifications and Compliance

CE Compliant	CE Marked
CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506