



* Representative image

TF279261S

by Acme Electric

Catalog ID: TF279261S

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 190/208/220/240 / 380/416/440/480 - 120/240V, 2kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

CE Compliant	CE Marked
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	190 / 208 / 220 / 240 X 380 / 416 / 440 / 480 V
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503400029
Winding Material	CU
kVA	2

Dimensions

Height	13 in
Length	5.13 in
Weight	38 lb
Width	5.5 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	190/208/220/240 X 380/416/440/480 V

Certifications and Compliance

CE Compliant	CE Marked
CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R

UL Standard	UL 506
-------------	--------