

TSC2/0-1/0K

by CMC

Catalog ID: TSC2/0-1/0K

Compression Cable Splice with 600 Volt EPDM Rubber Cover



- Splice kits include a ready-to-use compression sleeve splice, a type TSC splice cover of EPDM rubber, a pack of silicon, grease, and an instruction sheet.
- Aluminum sleeves are intended for splicing aluminum to aluminum or aluminum to copper wires
- Can be used for completely submersed, direct burial, cable tray, or other 600-volt applications

Product Details

General

Die Size	<ul style="list-style-type: none"> • Kearney K840 • Burndy 249 • EEI 11A • T&B TX • T&B 76 • Anderson VC6
Material	Aluminum
Type	TSC-K

Dimensions

Length	10.8 in
--------	---------

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor - ACSR Cmpst Size A	3/0
Conductor - AL Str Size A	2/0
Conductor - Copper Str Size A	2/0



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

