

To Whom it May Concern:

Effective immediately, the StrateLine™ series of plugs and receptacles has been discontinued by Hubbell. This change was made due to low sales, obsolete designs, and other mitigating factors. Hubbell Killark (sister company to Vantage Technology, manufacturer of the StrateLine™ series) has a line of plugs and receptacles that is similar in form, fit, and function. The Killark KP/KR line of plugs and receptacles is also similar with respect to electrical ratings (i.e. voltage, amperage, horsepower ratings, etc).

Note: Though the Killark KP/KR line of plugs and receptacles carry similar ratings and are aesthetically similar to the Vantage Technology StrateLine™ series, they are not intermateable. Therefore, any installed equipment will need to be replaced with current equipment to maintain proper ratings.

Below is a cross-reference to help customers upgrade their specifications to the up-to-date product offerings:

StrateLine™ Series Part Number	Part Description	Electrical Ratings	Killark KP/KR Series Part Number
20A Configurations			
ERRA-11532 (45°) ERHA-11532 (90°)	20A, Single, 2-Pole/3-Wire Receptacle w/ 1/2" Dead-End Back Box	20A/1HP @ 120/240VAC	KRS-215-120
ERRA-21532 (45°) ERHA-21532 (90°)	20A, Single, 2-Pole/3-Wire Receptacle w/ 3/4" Dead-End Back Box	20A/1HP @ 120/240VAC	KRS-215-220
ERRA-31532 (45°) ERHA-31532 (90°)	20A, Single, 2-Pole/3-Wire Receptacle w/ 1" Dead-End Back Box	20A/1HP @ 120/240VAC	KRS-215-320
ERRA-115322 (45°) ERHA-115322 (90°)	20A, Duplex, 2-Pole/3-Wire Receptacle w/ 1/2" Dead-End Back Box	20A/1HP @ 120/240VAC	2KRS-215-120
ERRA-215322 (45°) ERHA-215322 (90°)	20A, Duplex, 2-Pole/3-Wire Receptacle w/ 3/4" Dead-End Back Box	20A/1HP @ 120/240VAC	2KRS-215-220
ERRA-315322 (45°) ERHA-315322 (90°)	20A, Duplex, 2-Pole/3-Wire Receptacle w/ 1" Dead-End Back Box	20A/1HP @ 120/240VAC	2KRS-215-320
ERRC-115322(45°) ERHC-115322 (90°)	20A, Duplex, 2-Pole/3-Wire Receptacle w/ 1/2" Feed-Thru Back Box	20A/1HP @ 120/240VAC	2KRS-218-120
ERRC-215322(45°) ERHC-215322 (90°)	20A, Duplex, 2-Pole/3-Wire Receptacle w/ 3/4" Feed-Thru Back Box	20A/1HP @ 120/240VAC	2KRS-218-220
ERRC-315322(45°) ERHC-315322 (90°)	20A, Duplex, 2-Pole/3-Wire Receptacle w/ 1" Feed-Thru Back Box	20A/1HP @ 120/240VAC	2KRS-218-320
ERRA-11542 (45°) ERHA-11542 (90°)	20A, Single, 3-Pole/4-Wire Receptacle w/ 1/2" Dead-End Back Box	20A/1.5HP @ 120/240VAC	N/A
ERRA-21542 (45°) ERHA-21542 (90°)	20A, Single, 3-Pole/4-Wire Receptacle w/ 3/4" Dead-End Back Box	20A/1.5HP @ 120/240VAC	N/A
ERRA-31542 (45°) ERHA-31542 (90°)	20A, Single, 3-Pole/4-Wire Receptacle w/ 1" Dead-End Back Box	20A/1.5HP @ 120/240VAC	N/A
ERRA-115422 (45°) ERHA-115422 (90°)	20A, Duplex, 3-Pole/4-Wire Receptacle w/ 1/2" Dead-End Back Box	20A/1.5HP @ 120/240VAC	N/A
ERRA-215422 (45°) ERHA-215422 (90°)	20A, Duplex, 3-Pole/4-Wire Receptacle w/ 3/4" Dead-End Back Box	20A/1.5HP @ 120/240VAC	N/A
ERRA-315422 (45°) ERHA-315422 (90°)	20A, Duplex, 3-Pole/4-Wire Receptacle w/ 1" Dead-End Back Box	20A/1.5HP @ 120/240VAC	N/A
ERRC-115422(45°) ERHC-115422 (90°)	20A, Duplex, 3-Pole/4-Wire Receptacle w/ 1/2" Feed-Thru Back Box	20A/1.5HP @ 120/240VAC	N/A
ERRC-215422(45°) ERHC-215422 (90°)	20A, Duplex, 3-Pole/4-Wire Receptacle w/ 3/4" Feed-Thru Back Box	20A/1.5HP @ 120/240VAC	N/A
ERRC-315422(45°) ERHC-315422 (90°)	20A, Duplex, 3-Pole/4-Wire Receptacle w/ 1" Feed-Thru Back Box	20A/1.5HP @ 120/240VAC	N/A
EPD-51532	20A, 2-Pole/3-Wire Plug (.250-.625 Cord Range)	20A/1HP @ 120/240VAC	KP-20ABC
EPD-51542	20A, 3-Pole/4-Wire Plug (.250-.625 Cord Range)	20A/1HP @ 120/240VAC	N/A
30A Configurations			

ERRA-23032 (45°) ERHA-23032 (90°)	30A, Single, 2-Pole/3-Wire Receptacle w/ 3/4" Dead-End Back Box	30A/1.5HP @ 120/240VAC; 7A/.5HP @ 480VAC	KRS-215-2303
ERRA-33032 (45°) ERHA-33032 (90°)	30A, Single, 2-Pole/3-Wire Receptacle w/ 1" Dead-End Back Box	30A/1.5HP @ 120/240VAC; 7A/.5HP @ 480VAC	KRS-215-3303
ERRA-230322 (45°) ERHA-230322 (90°)	30A, Duplex, 2-Pole/3-Wire Receptacle w/ 3/4" Dead-End Back Box	30A/1.5HP @ 120/240VAC; 7A/.5HP @ 480VAC	N/A
ERRA-330322 (45°) ERHA-330322 (90°)	30A, Duplex, 2-Pole/3-Wire Receptacle w/ 1" Dead-End Back Box	30A/1.5HP @ 120/240VAC; 7A/.5HP @ 480VAC	N/A
ERRC-230322 (45°) ERHC-230322 (90°)	30A, Duplex, 2-Pole/3-Wire Receptacle w/ 3/4" Feed-Thru Back Box	30A/1.5HP @ 120/240VAC; 7A/.5HP @ 480VAC	N/A
ERRC-330322 (45°) ERHC-330322 (90°)	30A, Duplex, 2-Pole/3-Wire Receptacle w/ 1" Feed-Thru Back Box	30A/1.5HP @ 120/240VAC; 7A/.5HP @ 480VAC	N/A
EPD-53032	30A, 2-Pole/3-Wire Plug (.375-.625 Cord Range)	30A/1.5HP @ 120/240VAC; 7A/.5HP @ 480VAC	KP-303D23
EPD-73032	30A, 2-Pole/3-Wire Plug (.626-.875 Cord Range)	30A/1.5HP @ 120/240VAC; 7A/.5HP @ 480VAC	KP-303D45
ERRA-23042 (45°) ERHA-23042 (90°)	30A, Single, 3-Pole/4-Wire Receptacle w/ 3/4" Dead-End Back Box	30A/3HP @ 120/240VAC; 7A/.5HP @ 480VAC	KRS-215-2304
ERRA-33042 (45°) ERHA-33042 (90°)	30A, Single, 3-Pole/4-Wire Receptacle w/ 1" Dead-End Back Box	30A/3HP @ 120/240VAC; 7A/.5HP @ 480VAC	KRS-215-3304
ERRA-230422 (45°) ERHA-230422 (90°)	30A, Duplex, 3-Pole/4-Wire Receptacle w/ 3/4" Dead-End Back Box	30A/3HP @ 120/240VAC; 7A/.5HP @ 480VAC	N/A
ERRA-330422 (45°) ERHA-330422 (90°)	30A, Duplex, 3-Pole/4-Wire Receptacle w/ 1" Dead-End Back Box	30A/3HP @ 120/240VAC; 7A/.5HP @ 480VAC	N/A
ERRC-230422 (45°) ERHC-230422 (90°)	30A, Duplex, 3-Pole/4-Wire Receptacle w/ 3/4" Feed-Thru Back Box	30A/3HP @ 120/240VAC; 7A/.5HP @ 480VAC	N/A
ERRC-330422 (45°) ERHC-330422 (90°)	30A, Duplex, 3-Pole/4-Wire Receptacle w/ 1" Feed-Thru Back Box	30A/3HP @ 120/240VAC; 7A/.5HP @ 480VAC	N/A
EPD-53042	30A, 3-Pole/4-Wire Plug (.375-.625 Cord Range)	30A/3HP @ 120/240VAC; 7A/.5HP @ 480VAC	KP-304D23
EPD-73042	30A, 3-Pole/4-Wire Plug (.626-.875 Cord Range)	30A/3HP @ 120/240VAC; 7A/.5HP @ 480VAC	KP-304D45

If an item does not have an item listed in the cross-reference column in the table above, please contact Customer Service at <https://www.hubbell.com/killark/en/contactUs> or via phone at (314) 531-0460.

Sincerely,

Hubbell Harsh and Hazardous Marketing Team