



Aluminum Compression Terminal for 250 AL/CU, 4/0 6/1 ACSR, 300 COMPACT

by ANDERSON
Catalog ID: VAUL25012BN

Aluminum Compression Terminal for 250 AL/CU, 4/0 6/1 ACSR, 300 COMPACT, 2 HOLE

- Connectors are prefilled with rubber compatible inhibitor and sealed with color coded end caps.

* Representative image

Product Details

General

Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
Die Size	*See Resources / Downloads for die selection and installation instructions
Material	Aluminum
Material - Body	Aluminum
Number of Pad Holes	2
Plating	No
Style	Impact Extruded
UPC	096359334743

Dimensions

Diameter - Pad Bolt	0.5 in
Weight	0.196 lb

Conductor Related

Conductor Compatibility	ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;ACSR-Pigeon-3/0-6/1;ACSR-Penguin-4/0-6/1;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAC-Valerian-250-19;AAAC 6201 Alloy-Azusa-123.3-6/18;AAAC 6201 Alloy-Anaheim-155.4-6/18;AAAC 6201 Alloy-Amherst-195.7-6/18;AAAC 6201 Alloy-Alliance-246.9-6/18
Conductor Diameter (VersaCrimp) - Maximum	0.575 in
Conductor Diameter (VersaCrimp) - Minimum	0.336 in

Certifications and Compliance

UL Listed	No
-----------	----

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscshubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com