


# Compression Stirrup

by ANDERSON  
Catalog ID: VCLSC5021

VersaCrimp Copper Overhead Compression Stirrup

- For use with VersaCrimp tools only (VC6 and VC7 series).



\* Representative image

## Product Details

### General

Bolt Installation Torque (Recommended)	0 ft-lbs
Material - Body	Cast Copper Alloy
Material - Stirrup	Copper
Plating	No
Type	Stirrups
UPC	096359336976

### Dimensions

Copper Loop Size	0.325 in
Diameter - Stirrup Nominal Wire	1/0 Solid
Weight	0.980 lb
Width - Main Contact	5 in

### Conductor Related

Conductor Diameter - Maximum	0.419 in
Conductor Diameter - Minimum	0.258 in
Conductor Diameter Range	0.258 - 0.419

### Logistics

Carton Quantity	40 EA
Packaging Type	Box

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)