



* Representative image

Anchor, Rock, Grouted Rod 1-1/4in X 36in

by CHANCE Utility
Catalog ID: W1040004

Grouted Rock Anchor 1.25" (31.7 mm) Diameter Rod 3' (914 mm) long (Guy Adapter ordered separately).

- Used in situations where rock is fractured preventing the use of wedge style rock anchors.
- RR, SS5 or SS150 Extensions are used to extend anchor.
- Hot dipped galvanized per ASTM A153

Product Details

General

Coating	Galvanized
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5° of alignment with the guy load may significantly lower strength. Recommended minimum installation depth is 12" in solid rock.
Tensile Strength	70000 lb
Type	Rock Anchors
UPC	096359482185

Dimensions

Anchor Hole Size	6 in
Length	36.000 in
Rod Diameter	1.250 in
Weight	17.600 lb

Logistics

Pallet Quantity	40 EA
Standard Package	1

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com