



\* Representative image

# Anchor, Rock, Grouted Rod 1-1/4in X 84in

by CHANCE Utility  
Catalog ID: W1040055

Grouted Rock Anchor 1.25" (31.7 mm) Diameter Rod 7' (2134 mm) long (Guy Adapter ordered separately).

- Used in situations where rock is fractured preventing the use of wedge style rock anchors.
- RR, SS5 or SS150 Extensions are used to extend anchor.
- Hot dipped galvanized per ASTM A153

## Product Details

### General

Coating	Galvanized
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5° of alignment with the guy load may significantly lower strength. Recommended minimum installation depth is 12" in solid rock.
Tensile Strength	70000 lb
Type	Rock Anchors
UPC	096359482192

### Dimensions

Anchor Hole Size	6 in
Length	84.000 in
Rod Diameter	1.250 in
Weight	34.000 lb

### Logistics

Standard Package	1
------------------	---

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)