



WA080806GIE

by Wiegmann
Catalog ID: WA080806GIE

N12 JIC Hinged Screw-Cover 8X8X6 Carbon Steel - Gray

Designed for use as instrument housing, electrical control enclosures, terminal wiring boxes or electrical junction boxes. Provides protection from dirt, dust, oil, and water.

- Fabricated from 14 gauge steel. Continuously welded seams ground smooth, less knockouts or holes. Lids are sealed with closed cell oil resistant neoprene gasket. Cover is secured by continuous hinge. Captivated door screws thread into sealed wells. No mounting feet or mounting holes are provided. Weldnuts are provided to mount optional panels. Grounding provisions provided.

Product Details

General

Application	Designed for use as instrument housings, electrical control enclosures, terminal wiring boxes, or electrical junction boxes. Provides protection from dirt, dust, oil, and water.
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Hinged Screw Cover
Finish Type	Textured
Listings	UL, CSA
Material	Carbon Steel
Mounting Type	Wall Mount
Type	Enclosure
UPC	786725442355

Dimensions

Depth	6 in
Height	8 in
Weight	8.5 lb
Width	8 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	NEMA 12
UL Listed	Yes