



## WA121006GIE

by Wiegmann  
Catalog ID: WA121006GIE

N12 JIC Hinged Screw-Cover 12X10X6 Carbon Steel - Gray

Designed for use as instrument housing, electrical control enclosures, terminal wiring boxes or electrical junction boxes. Provides protection from dirt, dust, oil, and water.

- Fabricated from 14 gauge steel. Continuously welded seams ground smooth, less knockouts or holes.
- Lids are sealed with closed cell oil resistant neoprene gasket. Cover is secured by continuous hinge. Captivated door screws thread into sealed wells. No mounting feet or mounting holes are provided. Weldnuts are provided to mount optional panels. Grounding provisions provided.

## Product Details

### General

|               |   |
|---------------|---|
| Application   | Designed for use as instrument housings, electrical control enclosures, terminal wiring boxes, or electrical junction boxes. Provides protection from dirt, dust, oil, and water. |
| Color         | Gray  |
| Construction  | Continuously Welded Seams   |
| Cover Type    | Hinged Screw Cover  |
| Finish Type   | Textured  |
| Listings      | UL, CSA   |
| Material      | Carbon Steel  |
| Mounting Type | Wall Mount  |
| Type          | Enclosure   |
| UPC           | 786725442508  |

### Dimensions

|        |       |
|--------|-------|
| Depth  | 6 in  |
| Height | 12 in |
| Weight | 13 lb |
| Width  | 10 in |

### Certifications and Compliance

|                  |  |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul> |
| Nema Rating      | NEMA 12  |
| UL Listed        | Yes  |